



Model GZ-10

Gzunda

bed mover & trolley mover



Move hospital beds safely and efficiently

The Gzunda Bed Mover and Trolley mover allows one person to effortlessly move heavy hospital beds and trolleys. The motorised unit operates equally well with or without load - simplifying the task to moving beds or trolleys between wards, departments, or to and from theatre. This allows the driver to focus on the needs of the patient during transport.

With a capacity of 500kg, the silent motorised unit is able move a hospital bed up or down ramps, over carpet, into lifts, and around tight corner with minimal effort by the operator. The Gzunda's compact design, effortless maneuverability and detach-ability allows for safe and efficient management of a fleet of beds or trolleys within a healthcare environment.

Typical applications include:

- Moving hospital beds with or without patients between rooms and wards.
- Transporting patients to and from high traffic departments e.g. emergency, radiology and theatre
- Moving linen and Moving stock trolleys

- ☑ Capacity: 500 kg (customised units available for bariatric care).
- ☑ Move bed with or without patients safely and efficiently
- ☑ Push button hitching - silent, fast and efficient
- ☑ Quiet, smooth operation with zero emissions
- ☑ Simple to use, no driver's licence required



Replaces all previous versions

Effective 17th May 2011


Gzunda

bed mover & trolley mover

The Gzunda's easy to use controls includes; key start, 'twist grip' throttle (with adjustable height and reach), variable speed control, horn, and emergency stop button, and now with push button - Hitching.

With the healthcare environment in mind, the Gzunda body is made of tough, powdercoated steel with a scratch resistant Stainless Steel tyne.

And as with all Electrodrive equipment, the Gzunda comes with a **comprehensive 12 month warranty**, including parts and labour



Code	Descriptions	
# GZ-10 Gzunda Bed Mover & Trolley Mover	Height 1190 mm Length 1210 mm Width 655 mm Capacity 500 kg Weight 150 kg Voltage 24 v Range ~ 10 km	Please email to sales@spacepac.com.au For current pricing
Accessories		
# HT1700	Bed Gripper Set	
# HT1550	Trolley Clamps	



Drive speed of Gzunda:

Normally from 2.5 up to 4.5km/hr (fast walking speed)

The speed can be controlled at the Twist Grip or Tiller handle from nothing up to the maximum set on the speed governing Rheostat. We can factory program minimum and maximum speeds and reduce gearing as requested at time of ordering.

Push Button - Bed Hitching

